


USB"A"M


6FT(1830±20mm)

USB"B"M



Cable Marking:  
 USB SHIELDED HIGH SPEED CABLE 2.0  
 REVISION 28AWG/2C+22AWG/2C E119932-T  
 AWM 2725 80° 30V COPARTNER

PIN OUT:




TEST REQUEST

- 1.100% OPEN SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE 5 Ohms MAX
- 3.INSULATION RESISTANCE 5M Ohms MIN

1	CABLE:UL2725 1P*28#+2C*22#+1+AL+B (COPPER) BLACK OD4.8
2	CONNECTOR:USB AM PLATED NICKEL
3	CONNECTOR:USB BM PLATED NICKEL
4	TIN LINE:LEAD-FREE GREEN WIRE
5	OVER MODEL:PVC 45P BLACK

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL,  
 PROPRIETARY INFORMATION THAT IS  
 PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2HAB6		
DESCRIPTION	6 ft USB 2.0 CERTIFIED A TO B CABLE - M/M		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 03/31/2020