



PIN ASSIGNMENT

P1	WIRE TYPE	P2	COLOR
1		1	RED
2		2	WHITE
3		3	GREEN
4		4	BLACK
SHELL		SHELL	DRAIN

- NOTE:
1. OPEN/SHORT/INTERMITTENCE 100% TEST.
  2. DIELECTRIC STRENGTH:200 VOLTS AC 2mA MAX/0.02S.
  3. INSULATION RESISTANCE:300V DC/0.02SEC, 10MΩ MIN.
  4. CONDUCTIVE RESISTANCE:2Ω MAX.
  5. RoHS COMPLIANT.

SKU	LENGTH
USBEXTPAA1MW	1000MM±30MM
USBEXTPAA2MW	2000MM±40MM
USBEXTPAA3MW	3000MM±40MM

NO.	NAME	MATERIAL DESCRIPTION	Q'TY	UNITS
5	OVER MOLD	PVC , COLOR:WHITE	A/R	KG
4	INNER MOLD	LD-PE	A/R	KG
3	CONNECTOR	USB A/F 4PIN (180° SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	1	PCS
2	CONNECTOR	USB A/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	1	PCS
1	CABLE	USB 2.0 UL2725 28#(7/0.12TC)*1P+24#(7/0.12TC)*2C +D(7/0.12TC)+AL/MY OD:3.0mm C:WHITE PVC JACKET	A/R	M

THIRD ANGLE PROJECTION

**GENERAL NOTES**  
 DIMENSIONS ARE IN MM - DO NOT SCALE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

**PRODUCT ID** USBEXTPAAxxMW  
**DESCRIPTION** White USB 2.0 Extension Cable A to A - M/F

**DO NOT SCALE**    **SHEET: 1 OF: 1**    **UPLOAD DATE: 12/4/2020**