



- NOTE:**
1. OPEN/SHORT/INTERMITTENCE 100% TEST.
 2. DIELECTRIC STRENGTH:200 VOLTS AC 2mA MAX/0.02S.
 3. INSULATION RESISTANCE:300V DC/0.02SEC, 10MΩ MIN.
 4. CONDUCTIVE RESISTANCE:3Ω MAX.
 5. RoHS COMPLIANT.

PIN ASSIGNMENT

P1	WIRE TYPE	P2	COLOR
1		1	RED
2		2	WHITE
3		3	GREEN
4		4	BLACK
SHELL		SHELL	BRAIN

NO.	NAME	MATERIAL DESCRIPTION	Q'TY	UNITS
7	NUT	4#-40UNC,4.75*6.5MM	2	PCS
6	SCREW	4#-40UNC,L=6.5MM	2	PCS
5	INNER MOLD	LD-PE	A/R	KG
4	OVER MOLD	PVC , COLOR:BLACK	A/R	KG
3	CONNECTOR	USB A/F 4PIN (180° SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	2	PCS
2	CONNECTOR	USB A/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	2	SET
1	CABLE	UL 2725 28AWG*1P+24AWG*2C+AL/MY+ D(7/0.12TCCS)+B(65%AL-MG) OD:4.5MM BLACK PVCJACKET	A/R	M

THIRD ANGLE PROJECTION

GENERAL NOTES
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USBPFLAFAM2		
DESCRIPTION	2 ft Panel Mount USB Cable A to A - F/M		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 05/13/2020